

# 屋内照明器具特性

|         |                    |  |  |  |  |           |  |  |  |  |
|---------|--------------------|--|--|--|--|-----------|--|--|--|--|
| 品番 (品名) | NNQ35495K          |  |  |  |  |           |  |  |  |  |
| 光源      | LED3000_85_1525 x1 |  |  |  |  | 1525.0 lm |  |  |  |  |
| 管理番号    | K0190146(1)DR1     |  |  |  |  |           |  |  |  |  |
| BZ分類    | BZ1                |  |  |  |  |           |  |  |  |  |

| 器具効率   | 100%            | 天井      | 80%           |     |     |     | 70% |     |     |     | 50% |     |     |     | 30% |     |    |    | 0%  |    |
|--------|-----------------|---------|---------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|----|
|        |                 |         | 壁             | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50 | 30 | 10  | 0% |
| 上方光束   | 0%              | 床       | 10%           |     |     |     | 10% |     |     |     | 10% |     |     |     | 10% |     |    |    | 0%  |    |
| 下方光束   | 100%            | 室指数     | 照明率 ( X0.01 ) |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    | ZCM |    |
| 保守率    | 良               | 0.81    | 0.6           | 72  | 63  | 58  | 54  | 71  | 63  | 57  | 54  | 69  | 62  | 57  | 53  | 68  | 61 | 57 | 53  | 52 |
|        | 中               | 0.77    | 0.8           | 81  | 74  | 68  | 65  | 80  | 73  | 68  | 65  | 78  | 72  | 68  | 64  | 76  | 71 | 67 | 64  | 63 |
|        | 否               | 0.68    | 1.0           | 87  | 80  | 75  | 72  | 86  | 80  | 75  | 72  | 84  | 78  | 74  | 71  | 82  | 77 | 74 | 71  | 69 |
|        |                 |         | 1.25          | 91  | 86  | 81  | 78  | 90  | 85  | 81  | 77  | 88  | 83  | 80  | 77  | 86  | 82 | 79 | 76  | 75 |
| 下方投影面積 | cm <sup>2</sup> |         | 1.5           | 94  | 89  | 85  | 82  | 93  | 88  | 84  | 81  | 91  | 87  | 83  | 81  | 89  | 85 | 83 | 80  | 78 |
|        | 等価発光面積          |         | 2.0           | 98  | 94  | 90  | 87  | 97  | 93  | 90  | 87  | 94  | 91  | 88  | 86  | 92  | 90 | 87 | 85  | 83 |
| 取付高さ   | 器具間隔最大限         |         | 2.5           | 100 | 96  | 93  | 91  | 99  | 95  | 93  | 90  | 96  | 94  | 91  | 89  | 94  | 92 | 90 | 88  | 86 |
|        | 横方向 (A)         | 縦方向 (B) | 3.0           | 101 | 98  | 96  | 93  | 100 | 97  | 95  | 93  | 98  | 96  | 93  | 92  | 96  | 94 | 92 | 91  | 88 |
| Hm     | 1.21Hm          | 1.21Hm  | 4.0           | 103 | 101 | 99  | 97  | 102 | 100 | 98  | 96  | 100 | 98  | 96  | 95  | 97  | 96 | 95 | 93  | 91 |
|        |                 |         | 5.0           | 104 | 102 | 100 | 99  | 103 | 101 | 100 | 98  | 101 | 99  | 98  | 97  | 99  | 97 | 96 | 95  | 93 |
|        |                 |         | 7.0           | 105 | 104 | 103 | 101 | 104 | 103 | 102 | 100 | 102 | 101 | 100 | 99  | 100 | 99 | 98 | 97  | 95 |
|        |                 |         | 10.0          | 106 | 105 | 104 | 103 | 105 | 104 | 103 | 102 | 103 | 102 | 101 | 101 | 100 | 99 | 99 | 99  | 96 |

