




非常用照明器具特性



| | | | |
|--------------------|--------------------|---------|---------|
| 品番 | NNCF41135 (WALL) | | |
| 名称 | | | |
| 光源 | LED5000 / 97 / 435 | | |
| 管理番号 | K0185274(0) DB1 | | |
| 光束 | 870lm × 1.00 | | |
| 保守率 | 0.92 | | |
| 適用品番 | 設計照度Eを得るための読取照度 | | |
| | E = 2.0 | E = 1.0 | E = 0.5 |
| NNCF41135 (WALL) | 2.5 | 1.2 | 0.6 |
| 備考 | 非常点灯時の照度 (30分後) | | |



| | | | | | |
|------|------------------|--|--|----|-----------------|
| 品番 | NNCF41135 (WALL) | | | | |
| 名称 | | | | | |
| 光源 | LED5000/97/435 | | | | |
| 管理番号 | K0185274(0)DB 1 | | | | |
| 光束 | 870.0 1 m * 1.00 | | | 備考 | 非常点灯時の照度 (30分後) |
| 保守率 | 0.92 | | | | |

非常灯配置表

| | | | | | | | | | | | | | | | | | | | | |
|-------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m) | | | | | | | | | | | | | | | | | | | | |
| 単体配置 | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| 直線配置 | | | | | | | | | | | | | | | | | | | | |
| 四角配置 | | | | | | | | | | | | | | | | | | | | |
| 壁からの距離 (最大) | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |

| | | | | | | | | | | | | | | | | | | | | |
|-------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m) | | | | | | | | | | | | | | | | | | | | |
| 単体配置 | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| 直線配置 | | | | | | | | | | | | | | | | | | | | |
| 四角配置 | | | | | | | | | | | | | | | | | | | | |
| 壁からの距離 (最大) | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |

| | | | | | | | | | | | | | | | | | | | | |
|-------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m) | | | | | | | | | | | | | | | | | | | | |
| 単体配置 | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |
| 直線配置 | | | | | | | | | | | | | | | | | | | | |
| 四角配置 | | | | | | | | | | | | | | | | | | | | |
| 壁からの距離 (最大) | | | | | | | | | | | | | | | | | | | | |
| | | | | | | | | | | | | | | | | | | | | |

階段配置表

| 器具取付高さ (m) | | | 1.0 | 1.5 | 2.0 | 2.5 | 3.0 | 4.0 | 5.0 | 6.0 | 7.0 | 8.0 |
|------------|-------|----|-----|-----|-----|-----|------|------|------|------|------|------|
| Y=1.0 (m) | 2.0Lx | X+ | 5.4 | 6.4 | 7.1 | 7.8 | 8.4 | 9.1 | 9.2 | 9.0 | 0.3 | 0.1 |
| | | X- | 0.1 | 0.1 | 0.1 | 0.1 | 0.3 | 0.2 | 0.2 | 0.2 | 0.2 | 0.0 |
| Y=1.5 (m) | 2.0Lx | X+ | 6.7 | 8.0 | 9.0 | 9.9 | 10.6 | 11.8 | 12.5 | 13.0 | 13.1 | 13.0 |
| | | X- | 0.1 | 0.1 | 0.2 | 0.3 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.0 |
| Y=2.0 (m) | 2.0Lx | X+ | 4.6 | 5.8 | 6.8 | 7.7 | 8.3 | 9.0 | 9.1 | 8.6 | 0.3 | 0.1 |
| | | X- | 0.1 | 0.1 | 0.1 | 0.2 | 0.3 | 0.3 | 0.2 | 0.2 | 0.2 | 0.0 |
| | 1.0Lx | X+ | 6.4 | 7.7 | 8.7 | 9.6 | 10.4 | 11.7 | 12.5 | 13.0 | 13.1 | 13.0 |