

# 屋内照明器具特性

|         |                   |          |
|---------|-------------------|----------|
| 品番 (品名) | NNQ35518          |          |
| 光源      | LED4000_85_955 ×1 | 955.0 lm |
| 管理番号    | K0171181(0)DR1    |          |
| BZ分類    | BZ1               |          |

| 器具効率             | 100%            | 天井      | 80%  |     |     |     | 70%         |     |     |     | 50% |     |     |     | 30% |     |     |     | 0% |  |  |  |
|------------------|-----------------|---------|------|-----|-----|-----|-------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|--|--|--|
|                  |                 |         | 70   | 50  | 30  | 10  | 70          | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |    |  |  |  |
| 上方光束             | 0%              | 反射率     | 10%  |     |     |     | 10%         |     |     |     | 10% |     |     |     | 10% |     |     |     | 0% |  |  |  |
| 下方光束             | 100%            |         | 室指数  |     |     |     | 照明率 (X0.01) |     |     |     |     |     |     |     |     |     |     |     |    |  |  |  |
| 保守率              | 良 0.81          | 0.6     | 90   | 85  | 82  | 80  | 89          | 85  | 82  | 80  | 88  | 84  | 82  | 80  | 87  | 84  | 82  | 80  | 79 |  |  |  |
|                  | 中 0.77          | 0.8     | 95   | 90  | 88  | 86  | 94          | 90  | 87  | 85  | 93  | 89  | 87  | 85  | 92  | 89  | 87  | 85  | 84 |  |  |  |
|                  | 否 0.68          | 1.0     | 98   | 94  | 91  | 89  | 97          | 93  | 91  | 89  | 95  | 92  | 90  | 89  | 94  | 92  | 90  | 88  | 87 |  |  |  |
| 下方投影面積<br>等価発光面積 | cm <sup>2</sup> | 1.25    | 100  | 97  | 94  | 92  | 99          | 96  | 94  | 92  | 97  | 95  | 93  | 91  | 96  | 94  | 92  | 91  | 90 |  |  |  |
|                  |                 | 1.5     | 101  | 98  | 96  | 94  | 100         | 98  | 96  | 94  | 99  | 97  | 95  | 93  | 97  | 95  | 94  | 93  | 91 |  |  |  |
|                  |                 | 2.0     | 103  | 101 | 99  | 97  | 102         | 100 | 98  | 97  | 100 | 99  | 97  | 96  | 99  | 97  | 96  | 95  | 93 |  |  |  |
| 取付高さ             | 器具間隔最大限         |         | 2.5  | 104 | 102 | 100 | 99          | 103 | 101 | 100 | 99  | 101 | 100 | 99  | 100 | 98  | 97  | 96  | 95 |  |  |  |
|                  | 横方向 (A)         | 縦方向 (B) | 3.0  | 105 | 103 | 102 | 100         | 104 | 102 | 101 | 100 | 102 | 101 | 100 | 99  | 100 | 99  | 98  | 97 |  |  |  |
| Hm               | 0.81Hm          | 0.81Hm  | 4.0  | 106 | 105 | 103 | 102         | 105 | 104 | 102 | 101 | 103 | 102 | 101 | 100 | 101 | 100 | 99  |    |  |  |  |
|                  |                 |         | 5.0  | 106 | 105 | 104 | 103         | 105 | 104 | 103 | 103 | 103 | 103 | 102 | 101 | 101 | 101 | 100 |    |  |  |  |
|                  |                 |         | 7.0  | 107 | 106 | 105 | 105         | 106 | 105 | 105 | 104 | 104 | 103 | 103 | 102 | 102 | 101 | 101 |    |  |  |  |
|                  |                 |         | 10.0 | 108 | 107 | 106 | 106         | 106 | 106 | 105 | 105 | 104 | 104 | 103 | 103 | 102 | 102 | 101 |    |  |  |  |

