

# 屋内照明器具特性

|         |                     |  |           |  |  |
|---------|---------------------|--|-----------|--|--|
| 品番 (品名) | XAD3 1 0 0 4 K      |  |           |  |  |
| 光源      | LLD4 0 0 0 4 CQ1 ×1 |  | 845.0 l m |  |  |
| 管理番号    | K0175549 ( 0 ) DR 1 |  |           |  |  |
| B Z 分類  | BZ4 / 0.7 / BZ3     |  |           |  |  |

|        |          |                 |               |    |    |    |      |    |    |    |      |    |    |    |      |    |    |    |     |    |
|--------|----------|-----------------|---------------|----|----|----|------|----|----|----|------|----|----|----|------|----|----|----|-----|----|
| 器具効率   | 83 %     | 天井              | 80 %          |    |    |    | 70 % |    |    |    | 50 % |    |    |    | 30 % |    |    |    | 0 % |    |
|        |          | 壁               | 70            | 50 | 30 | 10 | 70   | 50 | 30 | 10 | 70   | 50 | 30 | 10 | 70   | 50 | 30 | 10 | 0 % |    |
| 上方光束   | 0 %      | 床               | 10 %          |    |    |    | 10 % |    |    |    | 10 % |    |    |    | 10 % |    |    |    | 0 % |    |
| 下方光束   | 83 %     | 室指数             | 照明率 ( X0.01 ) |    |    |    |      |    |    |    |      |    |    |    |      |    |    |    | ZCM |    |
| 保守率    | 良        | 0.67            | 0.6           | 51 | 41 | 35 | 31   | 50 | 41 | 35 | 31   | 48 | 40 | 35 | 31   | 46 | 39 | 34 | 31  | 29 |
|        | 中        | 0.63            | 0.8           | 59 | 51 | 45 | 41   | 58 | 50 | 45 | 41   | 56 | 49 | 44 | 40   | 54 | 48 | 44 | 40  | 39 |
|        | 否        | 0.56            | 1.0           | 65 | 57 | 52 | 48   | 64 | 57 | 51 | 47   | 62 | 55 | 51 | 47   | 60 | 54 | 50 | 47  | 45 |
|        |          |                 | 1.25          | 70 | 63 | 58 | 54   | 69 | 62 | 57 | 54   | 66 | 61 | 57 | 53   | 64 | 60 | 56 | 53  | 51 |
| 下方投影面積 |          | cm <sup>2</sup> | 1.5           | 73 | 67 | 62 | 58   | 72 | 66 | 62 | 58   | 69 | 65 | 61 | 58   | 67 | 63 | 60 | 57  | 55 |
| 等価発光面積 |          | cm <sup>2</sup> | 2.0           | 77 | 72 | 68 | 65   | 76 | 71 | 67 | 64   | 74 | 70 | 66 | 64   | 72 | 68 | 65 | 63  | 61 |
| 取付高さ   | 器具間隔最大限  |                 | 2.5           | 80 | 75 | 72 | 69   | 78 | 75 | 71 | 68   | 76 | 73 | 70 | 68   | 74 | 71 | 69 | 67  | 65 |
|        | 横方向 (A)  | 縦方向 (B)         | 3.0           | 81 | 78 | 75 | 72   | 80 | 77 | 74 | 71   | 78 | 75 | 73 | 70   | 76 | 74 | 71 | 70  | 68 |
| H m    | 1.25 H m | 1.25 H m        | 4.0           | 83 | 81 | 78 | 76   | 82 | 80 | 77 | 75   | 80 | 78 | 76 | 74   | 78 | 76 | 75 | 73  | 71 |
|        |          |                 | 5.0           | 85 | 82 | 80 | 78   | 84 | 81 | 79 | 78   | 81 | 80 | 78 | 76   | 79 | 78 | 77 | 75  | 73 |
|        |          |                 | 7.0           | 86 | 84 | 83 | 81   | 85 | 83 | 82 | 81   | 83 | 82 | 80 | 79   | 81 | 80 | 79 | 78  | 76 |
|        |          |                 | 10.0          | 87 | 86 | 85 | 84   | 86 | 85 | 84 | 83   | 84 | 83 | 82 | 81   | 82 | 81 | 81 | 80  | 78 |

