

# 屋内照明器具特性

|         |                |    |       |    |  |
|---------|----------------|----|-------|----|--|
| 品番 (品名) | XSLD102LS      |    |       |    |  |
| 光源      | LED2700_70_700 | x1 | 700.0 | 1m |  |
| 管理番号    | K0166804(0)DB1 |    |       |    |  |
| BZ分類    | BZ4/0.7/BZ3    |    |       |    |  |

|        |            |                 |               |     |     |     |     |     |     |     |     |     |     |    |     |     |    |    |     |    |
|--------|------------|-----------------|---------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|-----|-----|----|----|-----|----|
| 器具効率   | 100%       | 天井              | 80%           |     |     |     | 70% |     |     |     | 50% |     |     |    | 30% |     |    |    | 0%  |    |
|        | 上方光束<br>0% |                 | 反射率           | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30 | 10  | 70  | 50 | 30 | 10  | 0% |
| 下方光束   | 100%       | 床               |               | 10% |     |     |     | 10% |     |     |     | 10% |     |    |     | 10% |    |    |     | 0% |
| 室指数    |            |                 | 照明率 ( X0.01 ) |     |     |     |     |     |     |     |     |     |     |    |     |     |    |    | ZCM |    |
| 保守率    | 良          | 0.67            | 0.6           | 61  | 50  | 43  | 38  | 60  | 49  | 42  | 38  | 58  | 48  | 42 | 37  | 56  | 47 | 42 | 37  | 36 |
|        | 中          | 0.63            | 0.8           | 72  | 61  | 54  | 49  | 70  | 61  | 54  | 49  | 68  | 59  | 53 | 49  | 66  | 58 | 53 | 49  | 47 |
|        | 否          | 0.56            | 1.0           | 78  | 69  | 62  | 57  | 77  | 68  | 62  | 57  | 74  | 67  | 61 | 57  | 72  | 66 | 61 | 57  | 55 |
|        |            |                 | 1.25          | 84  | 76  | 70  | 65  | 83  | 75  | 69  | 65  | 80  | 74  | 68 | 64  | 78  | 72 | 68 | 64  | 62 |
| 下方投影面積 |            | cm <sup>2</sup> | 1.5           | 88  | 81  | 75  | 70  | 87  | 80  | 74  | 70  | 84  | 78  | 73 | 70  | 81  | 76 | 72 | 69  | 67 |
| 等価発光面積 |            | cm <sup>2</sup> | 2.0           | 93  | 87  | 82  | 78  | 92  | 86  | 82  | 78  | 89  | 84  | 80 | 77  | 86  | 82 | 79 | 76  | 74 |
| 取付高さ   | 器具間隔最大限    |                 | 2.5           | 96  | 91  | 87  | 83  | 95  | 90  | 86  | 83  | 92  | 88  | 85 | 82  | 90  | 86 | 83 | 81  | 78 |
|        | 横方向 (A)    | 縦方向 (B)         | 3.0           | 98  | 94  | 90  | 87  | 97  | 93  | 89  | 86  | 94  | 91  | 88 | 85  | 92  | 89 | 86 | 84  | 82 |
| Hm     | 1.25Hm     | 1.25Hm          | 4.0           | 101 | 97  | 94  | 92  | 99  | 96  | 93  | 91  | 97  | 94  | 92 | 90  | 94  | 92 | 90 | 88  | 86 |
|        |            |                 | 5.0           | 102 | 99  | 97  | 95  | 101 | 98  | 96  | 94  | 98  | 96  | 94 | 92  | 96  | 94 | 93 | 91  | 88 |
|        |            |                 | 7.0           | 104 | 102 | 100 | 98  | 103 | 101 | 99  | 97  | 100 | 99  | 97 | 96  | 98  | 97 | 95 | 94  | 91 |
|        |            |                 | 10.0          | 105 | 104 | 102 | 101 | 104 | 103 | 101 | 100 | 102 | 100 | 99 | 98  | 99  | 98 | 97 | 97  | 94 |

