

# 屋内照明器具特性

|         |                   |           |
|---------|-------------------|-----------|
| 品番 (品名) | XAD3405N          |           |
| 光源      | LED5000_70_630 x1 | 630.0 l m |
| 管理番号    | K0166926(0)D 1    |           |
| BZ分類    | BZ5               |           |

|        |                  |          |                  |     |     |     |      |     |     |     |      |     |    |    |      |    |    |    |     |    |
|--------|------------------|----------|------------------|-----|-----|-----|------|-----|-----|-----|------|-----|----|----|------|----|----|----|-----|----|
| 器具効率   | 100 %            | 天井       | 80 %             |     |     |     | 70 % |     |     |     | 50 % |     |    |    | 30 % |    |    |    | 0 % |    |
|        |                  | 壁        | 70               | 50  | 30  | 10  | 70   | 50  | 30  | 10  | 70   | 50  | 30 | 10 | 70   | 50 | 30 | 10 | 0 % |    |
| 上方光束   | 0 %              | 床        | 10 %             |     |     |     | 10 % |     |     |     | 10 % |     |    |    | 10 % |    |    |    | 0 % |    |
| 下方光束   | 100 %            | 室指数      | 照明率 ( X0.01 )    |     |     |     |      |     |     |     |      |     |    |    |      |    |    |    | ZCM |    |
| 保守率    | 良                | 0.67     | 0.6              | 57  | 45  | 37  | 32   | 56  | 45  | 37  | 32   | 54  | 43 | 37 | 32   | 51 | 42 | 36 | 32  | 30 |
|        | 中                | 0.63     | 0.8              | 67  | 56  | 48  | 42   | 66  | 55  | 48  | 42   | 63  | 54 | 47 | 42   | 61 | 53 | 46 | 42  | 40 |
|        | 否                | 0.56     | 1.0              | 74  | 63  | 56  | 50   | 72  | 63  | 55  | 50   | 69  | 61 | 55 | 50   | 67 | 59 | 54 | 49  | 47 |
|        |                  |          | 1.25             | 80  | 70  | 63  | 58   | 78  | 69  | 63  | 57   | 75  | 68 | 62 | 57   | 73 | 66 | 61 | 56  | 54 |
| 下方投影面積 | c m <sup>2</sup> |          | 1.5              | 84  | 75  | 69  | 63   | 82  | 74  | 68  | 63   | 79  | 72 | 67 | 62   | 77 | 71 | 66 | 62  | 59 |
|        | 等価発光面積           |          | c m <sup>2</sup> | 2.0 | 90  | 82  | 77   | 72  | 88  | 81  | 76   | 71  | 85 | 79 | 74   | 70 | 82 | 77 | 73  | 70 |
| 取付高さ   | 器具間隔最大限          |          | 2.5              | 93  | 87  | 82  | 77   | 92  | 86  | 81  | 77   | 89  | 84 | 80 | 76   | 86 | 82 | 78 | 75  | 72 |
|        | 横方向 (A)          | 縦方向 (B)  | 3.0              | 96  | 90  | 86  | 82   | 94  | 89  | 85  | 81   | 91  | 87 | 83 | 80   | 88 | 85 | 82 | 79  | 76 |
| H m    | 1.25 H m         | 1.25 H m | 4.0              | 99  | 94  | 91  | 87   | 97  | 93  | 90  | 87   | 94  | 91 | 88 | 85   | 92 | 89 | 86 | 84  | 81 |
|        |                  |          | 5.0              | 101 | 97  | 94  | 91   | 99  | 96  | 93  | 90   | 96  | 94 | 91 | 89   | 94 | 92 | 89 | 87  | 85 |
|        |                  |          | 7.0              | 103 | 100 | 98  | 96   | 101 | 99  | 97  | 95   | 99  | 97 | 95 | 93   | 96 | 95 | 93 | 91  | 89 |
|        |                  |          | 10.0             | 104 | 103 | 101 | 99   | 103 | 101 | 100 | 98   | 101 | 99 | 98 | 96   | 98 | 97 | 96 | 95  | 92 |

