

# 屋内照明器具特性

|         |                     |           |
|---------|---------------------|-----------|
| 品番 (品名) | SLB15785 + SLK22007 |           |
| 光源      | LLD2421LCB1 ×1      | 500.0 l m |
| 管理番号    | K0193000 (0) DB1    |           |
| BZ分類    | BZ1                 |           |

|                  |                  |          |      |      |     |     |      |      |     |     |      |      |    |    |      |      |    |    |     |     |
|------------------|------------------|----------|------|------|-----|-----|------|------|-----|-----|------|------|----|----|------|------|----|----|-----|-----|
| 器具効率             | 97 %             | 天井       | 80 % |      |     |     | 70 % |      |     |     | 50 % |      |    |    | 30 % |      |    |    | 0 % |     |
|                  | 上方光束<br>0 %      |          | 反射率  | 70   | 50  | 30  | 10   | 70   | 50  | 30  | 10   | 70   | 50 | 30 | 10   | 70   | 50 | 30 | 10  | 0 % |
| 下方光束             | 97 %             | 床        |      | 10 % |     |     |      | 10 % |     |     |      | 10 % |    |    |      | 10 % |    |    |     | 0 % |
| 室指数              | 照明率 ( X 0.01 )   |          |      |      |     |     |      |      |     |     |      |      |    |    |      |      |    |    |     | ZCM |
| 保守率              | 良                | 0.67     | 0.6  | 81   | 75  | 72  | 69   | 80   | 75  | 72  | 69   | 79   | 74 | 71 | 69   | 78   | 74 | 71 | 69  | 68  |
|                  | 中                | 0.63     | 0.8  | 87   | 82  | 79  | 76   | 86   | 82  | 78  | 76   | 85   | 81 | 78 | 76   | 84   | 80 | 77 | 75  | 74  |
|                  | 否                | 0.56     | 1.0  | 91   | 86  | 83  | 81   | 90   | 86  | 83  | 80   | 88   | 85 | 82 | 80   | 87   | 84 | 81 | 80  | 78  |
| 下方投影面積<br>等価発光面積 | c m <sup>2</sup> | 1.25     | 94   | 90   | 87  | 84  | 93   | 89   | 86  | 84  | 91   | 88   | 86 | 84 | 90   | 87   | 85 | 83 | 82  |     |
|                  |                  | 1.5      | 96   | 92   | 89  | 87  | 95   | 91   | 89  | 87  | 93   | 90   | 88 | 86 | 91   | 89   | 87 | 86 | 84  |     |
| 取付高さ             | 器具間隔最大限          |          | 2.0  | 98   | 95  | 93  | 91   | 97   | 94  | 92  | 91   | 95   | 93 | 91 | 90   | 93   | 92 | 90 | 89  | 87  |
|                  | 横方向 (A)          | 縦方向 (B)  | 2.5  | 99   | 97  | 95  | 93   | 98   | 96  | 94  | 93   | 96   | 95 | 93 | 92   | 95   | 93 | 92 | 91  | 89  |
| H m              | 0.41 H m         | 0.41 H m | 3.0  | 100  | 98  | 97  | 95   | 99   | 97  | 96  | 94   | 97   | 96 | 94 | 93   | 95   | 94 | 93 | 92  | 90  |
|                  |                  |          | 4.0  | 101  | 100 | 98  | 97   | 100  | 99  | 98  | 97   | 98   | 97 | 96 | 95   | 97   | 96 | 95 | 94  | 92  |
|                  |                  |          | 5.0  | 102  | 101 | 100 | 99   | 101  | 100 | 99  | 98   | 99   | 98 | 97 | 96   | 97   | 96 | 96 | 95  | 93  |
|                  |                  |          | 7.0  | 103  | 102 | 101 | 100  | 102  | 101 | 100 | 100  | 99   | 98 | 98 | 98   | 97   | 97 | 97 | 96  | 94  |
|                  |                  |          | 10.0 | 103  | 103 | 102 | 102  | 102  | 102 | 101 | 101  | 100  | 99 | 99 | 98   | 98   | 98 | 98 | 97  | 95  |

