




# 非常用照明器具特性



|                        |                        |         |         |
|------------------------|------------------------|---------|---------|
| 品番                     | XL F 4 3 3 CTN( WALL ) |         |         |
| 名称                     |                        |         |         |
| 光源                     | LED5000 / 98 / 480     |         |         |
| 管理番号                   | K0151852( 7 ) DR1      |         |         |
| 光束                     | 960lm x 1.00           |         |         |
| 保守率                    | 0.93                   |         |         |
| 適用品番                   | 設計照度Eを得るための読取照度        |         |         |
|                        | E = 2.0                | E = 1.0 | E = 0.5 |
| XL F 4 3 3 CTN( WALL ) | 2.2                    | 1.1     | 0.6     |
|                        |                        |         |         |
|                        |                        |         |         |
| 備考                     | 非常点灯時の照度 ( 30 分後)      |         |         |



|      |                    |  |    |                 |
|------|--------------------|--|----|-----------------|
| 品番   | XLF433CTN( WALL )  |  |    |                 |
| 名称   |                    |  |    |                 |
| 光源   | LED5000 / 98 / 480 |  |    |                 |
| 管理番号 | K0151852( 7 ) DR 1 |  |    |                 |
| 光束   | 960.0 l m * 1.00   |  | 備考 | 非常点灯時の照度 (30分後) |
| 保守率  | 0.93               |  |    |                 |

非常灯配置表

|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|----------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m)     |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 単体配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 直線配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 四角配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 壁からの距離<br>(最大) |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |

|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|----------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m)     |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 単体配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 直線配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 四角配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 壁からの距離<br>(最大) |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |

|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|----------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 器具取付高さ (m)     |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 単体配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 直線配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 四角配置           |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 壁からの距離<br>(最大) |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|                |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |

階段配置表

|             |       |    |     |     |     |     |      |      |      |      |  |  |
|-------------|-------|----|-----|-----|-----|-----|------|------|------|------|--|--|
| 器具取付高さ (m)  |       |    | 1.0 | 1.5 | 2.0 | 2.5 | 3.0  | 4.0  | 5.0  | 6.0  |  |  |
| Y=1.0 ( m ) | 2.0Lx | X+ | 5.3 | 6.1 | 6.7 | 7.3 | 7.8  | 8.5  | 9.0  | 9.4  |  |  |
|             |       | X- | 0.3 | 0.3 | 0.5 | 0.6 | 0.7  | 0.8  | 0.6  | 0.2  |  |  |
|             | 1.0Lx | X+ | 6.7 | 7.8 | 8.7 | 9.4 | 10.0 | 11.0 | 11.8 | 12.4 |  |  |
| Y=1.5 ( m ) | 2.0Lx | X+ | 4.9 | 5.8 | 6.5 | 7.1 | 7.6  | 8.4  | 8.9  | 9.2  |  |  |
|             |       | X- | 0.1 | 0.3 | 0.4 | 0.5 | 0.6  | 0.7  | 0.5  | 0.1  |  |  |
|             | 1.0Lx | X+ | 6.5 | 7.6 | 8.4 | 9.2 | 9.8  | 10.8 | 11.6 | 12.3 |  |  |
| Y=2.0 ( m ) | 2.0Lx | X+ | 4.5 | 5.4 | 6.2 | 6.8 | 7.3  | 8.1  | 8.7  |      |  |  |
|             |       | X- | 0.0 | 0.2 | 0.3 | 0.4 | 0.5  | 0.6  | 0.3  |      |  |  |
|             | 1.0Lx | X+ | 6.1 | 7.2 | 8.1 | 8.9 | 9.5  | 10.6 | 11.5 |      |  |  |