

# 屋内照明器具特性

|         |                    |          |
|---------|--------------------|----------|
| 品番 (品名) | XND2007WW          |          |
| 光源      | LED4000_85_1925 ×1 | 1925.0lm |
| 管理番号    | K0176490(0)DB1     |          |
| BZ分類    | BZ1                |          |

|        |                  |         |      |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |     |
|--------|------------------|---------|------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|-----|
| 器具効率   | 100%             | 天井      | 80%  |     |     |     | 70% |     |     |     | 50% |     |     |     | 30% |     |     |    | 0% |    |     |
|        | 上方光束<br>0%       |         | 反射率  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30 | 10 | 0% |     |
| 下方光束   | 100%             | 床       |      | 10% |     |     |     | 10% |     |     |     | 10% |     |     |     | 10% |     |    |    | 0% |     |
| 室指数    | 照明率 (X0.01)      |         |      |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    | ZCM |
| 保守率    | 良<br>中<br>否      | 0.81    | 0.6  | 73  | 64  | 58  | 55  | 72  | 64  | 58  | 55  | 70  | 63  | 58  | 54  | 68  | 62  | 57 | 54 | 53 |     |
|        |                  | 0.77    | 0.8  | 82  | 74  | 69  | 65  | 81  | 74  | 69  | 65  | 79  | 73  | 68  | 65  | 77  | 72  | 68 | 65 | 63 |     |
|        |                  | 0.68    | 1.0  | 87  | 81  | 76  | 72  | 86  | 80  | 76  | 72  | 84  | 79  | 75  | 72  | 82  | 78  | 74 | 71 | 70 |     |
|        |                  |         | 1.25 | 92  | 86  | 82  | 78  | 91  | 85  | 81  | 78  | 88  | 84  | 80  | 77  | 86  | 83  | 79 | 77 | 75 |     |
| 下方投影面積 | c m <sup>2</sup> | 1.5     | 94   | 89  | 85  | 82  | 93  | 89  | 85  | 82  | 91  | 87  | 84  | 81  | 89  | 86  | 83  | 81 | 79 |    |     |
|        |                  | 2.0     | 98   | 94  | 90  | 88  | 97  | 93  | 90  | 87  | 95  | 91  | 89  | 86  | 93  | 90  | 88  | 86 | 84 |    |     |
| 取付高さ   | 器具間隔最大限          |         | 2.5  | 100 | 97  | 94  | 91  | 99  | 96  | 93  | 91  | 97  | 94  | 92  | 90  | 95  | 92  | 90 | 89 | 87 |     |
|        | 横方向 (A)          | 縦方向 (B) | 3.0  | 102 | 99  | 96  | 94  | 100 | 98  | 95  | 93  | 98  | 96  | 94  | 92  | 96  | 94  | 92 | 91 | 89 |     |
| H m    | 1.17H m          | 1.17H m | 4.0  | 103 | 101 | 99  | 97  | 102 | 100 | 98  | 96  | 100 | 98  | 96  | 95  | 98  | 96  | 95 | 94 | 91 |     |
|        |                  |         | 5.0  | 104 | 102 | 101 | 99  | 103 | 101 | 100 | 98  | 101 | 99  | 98  | 97  | 99  | 98  | 96 | 95 | 93 |     |
|        |                  |         | 7.0  | 106 | 104 | 103 | 102 | 104 | 103 | 102 | 101 | 102 | 101 | 100 | 99  | 100 | 99  | 98 | 97 | 95 |     |
|        |                  |         | 10.0 | 106 | 105 | 104 | 104 | 105 | 104 | 103 | 103 | 103 | 102 | 101 | 101 | 100 | 100 | 99 | 99 | 96 |     |

