

# 屋内照明器具特性

|         |                              |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
|---------|------------------------------|--|--|--|--|--|--|--|--|--|--|--|--|--|--|
| 品番 (品名) | XNN1531PW                    |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 光源      | LED4000_85_1100 x1 1100.0 1m |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| 管理番号    | K0192368(0)DB1               |  |  |  |  |  |  |  |  |  |  |  |  |  |  |
| BZ分類    | BZ5/0.7/BZ4                  |  |  |  |  |  |  |  |  |  |  |  |  |  |  |

|        |                            |         |                  |     |     |     |     |     |     |     |     |     |    |    |     |    |    |    |    |    |
|--------|----------------------------|---------|------------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|----|----|----|----|----|
| 器具効率   | 100%                       | 天井      | 80%              |     |     |     | 70% |     |     |     | 50% |     |    |    | 30% |    |    |    | 0% |    |
|        |                            | 壁       | 70               | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 70  | 50  | 30 | 10 | 70  | 50 | 30 | 10 | 0% |    |
| 上方光束   | 0%                         | 床       | 10%              |     |     |     | 10% |     |     |     | 10% |     |    |    | 10% |    |    |    | 0% |    |
| 下方光束   | 100%                       | 室指数     | 照明率 ( X0.01) ZCM |     |     |     |     |     |     |     |     |     |    |    |     |    |    |    |    |    |
| 保守率    | 良 0.83<br>中 0.81<br>否 0.77 | 0.6     | 58               | 47  | 39  | 34  | 57  | 46  | 39  | 34  | 55  | 45  | 38 | 33 | 53  | 44 | 38 | 33 | 31 |    |
|        |                            | 0.8     | 69               | 58  | 50  | 44  | 67  | 57  | 50  | 44  | 65  | 55  | 49 | 44 | 62  | 54 | 48 | 44 | 42 |    |
|        |                            | 1.0     | 75               | 65  | 58  | 52  | 74  | 64  | 57  | 52  | 71  | 63  | 56 | 52 | 68  | 61 | 56 | 51 | 49 |    |
|        |                            | 1.25    | 81               | 72  | 65  | 60  | 80  | 71  | 65  | 59  | 77  | 69  | 64 | 59 | 74  | 68 | 63 | 59 | 56 |    |
| 下方投影面積 | cm <sup>2</sup>            | 1.5     | 85               | 77  | 70  | 65  | 84  | 76  | 70  | 65  | 81  | 74  | 69 | 64 | 78  | 72 | 68 | 64 | 61 |    |
|        |                            | 2.0     | 91               | 84  | 78  | 73  | 89  | 83  | 77  | 73  | 86  | 81  | 76 | 72 | 83  | 79 | 75 | 71 | 69 |    |
| 取付高さ   | 器具間隔最大限                    |         | 2.5              | 94  | 88  | 83  | 79  | 92  | 87  | 82  | 78  | 90  | 85 | 81 | 77  | 87 | 83 | 80 | 76 | 74 |
|        | 横方向 (A)                    | 縦方向 (B) | 3.0              | 96  | 91  | 87  | 83  | 95  | 90  | 86  | 82  | 92  | 88 | 84 | 81  | 89 | 86 | 83 | 80 | 78 |
| Hm     | 1.23Hm                     | 1.23Hm  | 4.0              | 99  | 95  | 92  | 88  | 98  | 94  | 91  | 88  | 95  | 92 | 89 | 86  | 92 | 90 | 87 | 85 | 83 |
|        |                            |         | 5.0              | 101 | 98  | 95  | 92  | 100 | 97  | 94  | 91  | 97  | 94 | 92 | 90  | 94 | 92 | 90 | 88 | 86 |
|        |                            |         | 7.0              | 103 | 101 | 98  | 96  | 102 | 99  | 97  | 95  | 99  | 97 | 95 | 94  | 97 | 95 | 94 | 92 | 89 |
|        |                            |         | 10.0             | 105 | 103 | 101 | 100 | 103 | 102 | 100 | 99  | 101 | 99 | 98 | 97  | 98 | 97 | 96 | 95 | 92 |

